

ZL9006MIRZ

Juote

ZL9006MIRZ Information

Heisener.com	Part Number Manufacturer Category		
	Description	DC/DC CONVERT 0.6-3.3V 6A 20W	- \$20,23
	Package	32-SMD Module	- FERSON
		For the pricing/inventory/lead time, please contact	
For Reference Only		us Website: https://www.heisener.com E-mail: salesdept@heisener.com	Request a Qu

Certified Quality

Heisener's commitment to quality has shaped our processes for sourcing, testing, shipping, and every step in between. This foundation underlies each component we sell.



ZL9006MIRZ Specifications

Manufacturer Part Number	ZL9006MIRZ					
Manufacturer	Intersil					
Category	Power Supplies - Board Mount					
	DC DC Converters					
Package	32-SMD Module					
Series	ZL9006M					
Туре	Non-Isolated PoL Module, Digital					
Number of Outputs	1					
Voltage - Input (Min)	4.5V					
Voltage - Input (Max)	13.2V					
Voltage - Output 1	0.6 ~ 3.3 V					
Voltage - Output 2	-					
Voltage - Output 3	-					
Voltage - Output 4	-					
Current - Output (Max)	6A					
Power (Watts)	-					
Voltage - Isolation	-					
Applications	ITE (Commercial)					
Features	OCP, OTP, OVP, UVLO					
Operating Temperature	$-40^{\circ}\mathrm{C} \sim 85^{\circ}\mathrm{C}$					
Efficiency	-					
Mounting Type	Surface Mount					
Package / Case	32-SMD Module					
Size / Dimension	0.68" L x 0.45" W x 0.10" H (17.2mm x 11.5mm x 2.5mm)					

Supplier Device Packa	ige	-					
Control Features		-					
						Report erro	ors?
ZL9006MIRZ G	uarantees						
QUALITY	Quality Guarantees We provide 90 days warranty. * If the items you received were not in perfect quality, we would be responsible for your refund or replacement, but the items must be returned in their original condition.						
SERVICE BUARANTEE	Service Guarantees We guarantee 100% customer satisfaction. Our experienced sales team and tech support team back our services to satisfy all our customers.						
ZL9006MIRZ Pa	yment Methoo	ls					
WIRE transfer	PayPal	WESTERN WU UNION WU moving money for better	S MoneyGram	Alipay	VISA MasterCard		ay R
ZL9006MIRZ Sł	ipping Metho	ls					
			🕫 TNT	TEMS	Contraction of the second seco		

If you have any question about ZL9006MIRZ, please do not hesitate to contact us! Website: https://www.heisener.com E-mail: salesdept@heisener.com